

# Heavy-duty tubing PAN-R-6X1,1-SI

Part number: 541675

FESTO



## Data sheet

| Feature                                  | Value                                                                 |
|------------------------------------------|-----------------------------------------------------------------------|
| Outside diameter                         | 6 mm                                                                  |
| Flow-relevant bending radius             | 21 mm                                                                 |
| Inside diameter                          | 3.8 mm                                                                |
| Min. bending radius                      | 16 mm                                                                 |
| Tubing characteristics                   | Suitable for energy chains                                            |
| Temperature-dependent operating pressure | -0.095 MPa...3.5 MPa<br>-0.95 bar...35 bar<br>-13.775 psi...507.5 psi |
| Approval                                 | German Technical Control Board (TÜV)                                  |
| Certificate issuing authority            | B 013277 0506 00                                                      |
| Operating medium                         | Compressed air to ISO 8573-1:2010 [7:-:-]                             |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                                                        |
| Ambient temperature                      | -30 °C...80 °C                                                        |
| Product weight according to length       | 0.0174 kg/m                                                           |
| Pneumatic connection                     | For push-in connector O.D. 6 mm                                       |
| Colour                                   | Silver                                                                |
| Shore hardness                           | D 62 +/-3                                                             |
| Note on materials                        | RoHS-compliant                                                        |
| Material tubing                          | TPE-A                                                                 |