

Heavy-duty tubing PAN-R-10X1,9-SI

Part number: 541677

FESTO



Data sheet

Feature	Value
Outside diameter	10 mm
Flow-relevant bending radius	44 mm
Inside diameter	6.2 mm
Min. bending radius	25 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa...3.5 MPa -0.95 bar...35 bar -13.775 psi...507.5 psi
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight according to length	0.0498 kg/m
Pneumatic connection	For push-in connector O.D. 10 mm
Colour	Silver
Shore hardness	D 62 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-A