

Multi-pin node VABE-S6-1LF-C-M1-R19

Part number: 543415

FESTO



Data sheet

Feature	Value
Mounting position	optional
Max. number of valve positions	16 with monostable valves 8 with bistable valves
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10 %
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C...50 °C
Product weight	539 g
Electrical control	Multi-pin plug
Electrical connection	19-pin Plugs To CNOMO E03.62.530.N
Material cover	PA
Material housing	Die-cast aluminium