

Branching module MS4-A-IPM-80

Part number: 543498

FESTO



Data sheet

Feature	Value
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Product weight	124 g
Note on materials	RoHS-compliant
Material sub-base	Die-cast aluminium
Material seals	NBR
Material hollow bolt	Die-cast aluminium
Material module connector	Die-cast aluminium
Material screws	Steel