

adapter NPFA-A-P18-G14-F

Part number: 545922

FESTO

For VUVB solenoid valves.



Data sheet

Feature	Value
Container size	10
Operating pressure	0.9 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-5 ... 50 °C
Product weight	20 g
Materials information for screw-in stud	Wrought Aluminium alloy
Materials note	Free of copper and PTFE Conforms to RoHS
Material information, blanking plug	Reinforced PA
Information on materials, O-ring	NBR
Material information, separator element	Steel