


Shock absorber DYSW-12-20-Y1F

Part number: 548075

FESTO



Data sheet

Feature	Value
Size	12
Stroke	20 mm
Cushioning	Self-adjusting Soft characteristic curve
Mounting position	optional
Position detection	Without
Max. impact speed	3 m/s
Reset time at room temperature	0.3 s
Reset time at min. ambient temperature	1 s
Mode of operation	Pushing Single-acting
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Cushioning length	20 mm
Max. stop force	1000 N
Max. energy consumption per stroke	12 J
Max. energy consumption per hour	41000 J
Max. residual energy	0.05 J
Reset force	5 N
Min. insertion force	35 N
Product weight	91 g
Load range	30 kg
Type of mounting	Via lock nut
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Galvanised steel
Material piston rod	High-alloy steel