

# Solenoid coil MH-2-230VAC-PA

Part number: 549908

FESTO



## Data sheet

Feature	Value
Mounting position	optional
Switching position indicator	no
Min. pick-up time	12 ms
Duty cycle	100%
Power factor (cos phi)	0.7
Characteristic coil data	230 V AC: 14.0 VA
Permissible frequency fluctuations	+/- 10%
Permissible voltage fluctuations	+/- 10 %
CE mark (see declaration of conformity)	To EU Low Voltage Directive
UKCA marking (see declaration of conformity)	To UK regulations for electrical equipment
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Note on degree of protection	IP00 without connector socket
Ambient temperature	-20 °C...50 °C
Max. tightening torque for fitting	2 Nm
Product weight	150 g
Electrical connection	To DIN EN 175301-803
Type of mounting	Via lock nut
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper