


# Gear unit

## EMGA-120-P-G5-SAS-140

Part number: 552199

FESTO



## Data sheet

| Feature                             | Value                  |
|-------------------------------------|------------------------|
| Gear unit flange size               | 120 mm                 |
| Motor flange size                   | 140 mm                 |
| Torsional backlash                  | 0.12 deg               |
| Type of gear unit                   | Planetary gear         |
| Gear unit ratio                     | 5:1                    |
| Max. drive speed                    | 6500 rpm               |
| Operating temperature of gear unit  | -25 °C...90 °C         |
| LABS (PWIS) conformity              | VDMA24364-B2-L         |
| Degree of protection                | IP54                   |
| Continuous output torque            | 195 Nm                 |
| Mass moment of inertia of gear unit | 1.53 kgcm <sup>2</sup> |
| Max. output torque                  | 312 Nm                 |
| Max. efficiency                     | 98 %                   |
| Torsional rigidity                  | 12 Nm/arcmin           |
| Product weight                      | 6000 g                 |
| Gear unit interface, output shaft   | 120G                   |
| Gear unit interface, drive shaft    | 140A                   |
| Note on materials                   | RoHS-compliant         |