


# Silencer UOS-1

Part number: 552252



## Data sheet

| Feature                        | Value                                    |
|--------------------------------|------------------------------------------|
| Type of seal on screwed plug   | No seal                                  |
| Mounting position              | optional                                 |
| Design                         | Open silencer                            |
| Operating pressure             | 0 MPa...1 MPa<br>0 bar...10 bar          |
| Operating medium               | Compressed air to ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress            |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                        |
| Sound pressure level           | 75 dB(A)                                 |
| Ambient temperature            | -10 °C...50 °C                           |
| Type of mounting               | Via male thread                          |
| Product weight                 | 200 g                                    |
| Pneumatic connection           | G1                                       |
| Material shock absorber insert | PE                                       |
| Note on materials              | RoHS-compliant                           |
| Material housing               | POM                                      |
| Material sleeve                | Wrought aluminium alloy                  |