

Fibre-optic cable
S00C-DS-C-M4-2-R15
Part number: 552842



Data sheet

Feature	Value
Note on materials	RoHS-compliant
Measurement method	Diffuse sensor
Min. object diameter	0.1 mm
Fibre-optic - special feature	Coaxial
Operating distance	75 mm
Ambient temperature	-55 °C...70 °C
Head size	M4
Fibre-optic length	2 m
Min. bending radius	15 mm
Max. tightening torque	2 Nm
Outside diameter	1.25 mm
Material housing	Brass, nickel-plated
Material fibre-optic	PE
Degree of protection	IP66
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III