

# Bellows kit DADB-V6-32-S251-300

Part number: 553279

FESTO



## Data sheet

| Feature                        | Value                                           |
|--------------------------------|-------------------------------------------------|
| Outside diameter               | 38 mm                                           |
| Size                           | 32                                              |
| Stroke range                   | 251 mm...300 mm                                 |
| Piston rod extension           | 96 mm                                           |
| Design                         | Round<br>Bellows kit<br>With ducted exhaust air |
| Mounting position              | optional                                        |
| Corrosion resistance class CRC | 3 - high corrosion stress                       |
| LABS (PWIS) conformity         | VDMA24364-B2-L                                  |
| Media resistance               | Dust<br>Chips<br>Oils<br>Grease<br>Petrol       |
| Degree of protection           | IP54                                            |
| Ambient temperature            | -10 °C...80 °C                                  |
| Product weight                 | 79 g                                            |
| Type of mounting               | Push-on<br>Via threaded pin                     |
| Pneumatic connection           | G1/8                                            |
| Note on materials              | RoHS-compliant                                  |
| Material adapter components    | PA-reinforced                                   |
| Material seals                 | NBR                                             |
| Material bellows               | NBR                                             |
| Material threaded pin          | High-alloy stainless steel                      |