

Bellows kit DADB-V6-40-S176-250

Part number: 553297

FESTO



Data sheet

Feature	Value
Outside diameter	46 mm
Size	40
Stroke range	176 mm...250 mm
Piston rod extension	72 mm
Design	Round Bellows kit With ducted exhaust air
Mounting position	optional
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C...80 °C
Product weight	85 g
Type of mounting	Push-on Via threaded pin
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Material adapter components	PA-reinforced
Material seals	NBR
Material bellows	NBR
Material threaded pin	High-alloy stainless steel