

Plastic tubing PEN

Part number: 553769

FESTO



Data sheet

Feature	Value
Outside diameter	4 mm...16 mm
Inside diameter	2.7 mm...10.8 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.95 bar...10 bar
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-30 °C...60 °C
Colour	Blue Yellow Green Natural Red Black Silver White
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant
Material tubing	PE