

Clevis foot LSN-32

Part number: 5561

FESTO



Data sheet

Feature	Value
Size	32
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...120 °C
Max. load capacity	0.9 kN
Product weight	162 g
Note on materials	RoHS-compliant
Material mounting	High-alloy steel
Material bushing	Wrought aluminium alloy
Material rod end bearing	Steel PTFE