

Drive shaft adapter
EAMB-34-6-25X26-23X27
Part number: 558037

FESTO



Data sheet

Feature	Value
Mounting diameter 1	25 mm
Mounting diameter 2	23 mm
Size	120
Nominal length	26 mm
Mounting position	optional
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	18.2 kgmm ²
Transmittable torque	100 Nm
Product weight	201 g
Note on materials	RoHS-compliant