

Drive shaft adapter
EAMB-44-7-35X30-32X32
Part number: 558038

FESTO



Data sheet

Feature	Value
Mounting diameter 1	35 mm
Mounting diameter 2	32 mm
Size	185
Nominal length	30 mm
Mounting position	optional
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	75.3 kgmm ²
Transmittable torque	200 Nm
Product weight	463 g
Note on materials	RoHS-compliant