

**Coupling**  
**EAMC-56-58-24-25**  
Part number: 558316

**FESTO**



**Data sheet**

| Feature                | Value                 |
|------------------------|-----------------------|
| Mounting diameter 1    | 24 mm                 |
| Mounting diameter 2    | 25 mm                 |
| Size                   | 56                    |
| Nominal length         | 58 mm                 |
| Mounting position      | optional              |
| Max. rotational speed  | 5500 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L        |
| Storage temperature    | -25 °C...60 °C        |
| Relative air humidity  | 0 - 95%               |
| Ambient temperature    | -25 °C...60 °C        |
| Mass moment of inertia | 128 kgmm <sup>2</sup> |
| Transmittable torque   | 60 Nm                 |
| Product weight         | 265 g                 |
| Note on materials      | RoHS-compliant        |