

Coupling
EAMC-20-30-6-6
Part number: 558901



Data sheet

Feature	Value
Mounting diameter 1	6 mm
Mounting diameter 2	6 mm
Size	20
Nominal length	30 mm
Mounting position	optional
Max. rotational speed	9000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C...60 °C
Mass moment of inertia	1.06 kgmm ²
Transmittable torque	2.3 Nm
Product weight	20 g
Note on materials	RoHS-compliant