


End plate VMPAL-EPL-SD25

Part number: 560938

FESTO



Data sheet

Feature	Value
Width	43 mm
Length	107.3 mm
Max. number of valve positions	24
Valve terminal structure	Valve sizes can be mixed
Max. number of valve coils	24
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pilot pressure	0.3 MPa...0.8 MPa 3 bar...8 bar
Nominal operating voltage DC	24 V
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP67
Note on degree of protection	In assembled state with accessories VMPAL-KM
Ambient temperature	-5 °C...50 °C
Product weight	190 g
Electrical connection 1, function	Multi-pin plug
Electrical connection 1, connection type	Plugs
Electrical connection 1, connector system	Sub-D
Electrical connection 1, number of connections/cores	25
Note on materials	RoHS-compliant
Material end plate	Die-cast aluminium PA-reinforced