

Plate VMPAL-EG-QS3/8"

Part number: 560959

FESTO



Data sheet

Feature	Value
Width	20.5 mm
Length	107.3 mm
Integrated function	Ducted exhaust air
Valve terminal structure	Valve sizes can be mixed
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Pressure regulation range	0.5 bar...5 bar
Inlet pressure 1	0.5 bar...10 bar
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	60 g
Pneumatic connection 3/5 combined	For tubing outside diameter of 3/8"
Note on materials	RoHS-compliant
Material plate	PA