

Electrical interlinking module

VMPAL-EVAP-10-2

Part number: 560962



Data sheet

Feature	Value
Valve size	10 mm
Max. number of valve positions	1
Max. number of valve coils	2
Integrated function	Colour-coded assignment of the valve function
Nominal operating voltage DC	24 V
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C...50 °C
Product weight	9 g
Housing colour	Black
Material housing	PA
Note on materials	RoHS-compliant