

Control block CPX-CM-HPP

Part number: 562214

FESTO



Data sheet

Feature	Value
Ambient temperature	-5 °C...50 °C
Product weight	140 g
CE mark (see declaration of conformity)	To EU Low Voltage Directive
Degree of protection	IP65 IP67
Storage temperature	-20 °C...70 °C
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364-B2-L
Power failure bridging	10 ms
Total number of axes	4
Dimensions (W x L x H)	50 x 107 x 55 mm
Control-Interface	CAN bus
Field bus interface	1x socket, M9, 5-pin
Device-specific diagnostics	Channel-oriented and module-oriented diagnostics Undervoltage/short circuit of modules Diagnostic memory
Configuration support	MMI handheld terminal
Parameterisation	Forcing of channels System parameter
Baud rate	1 Mbps
Operational voltage range DC	18 V...30 V
Nominal operating voltage DC	24 V
Protocol	FHPP
Intern power consumption nominal operating voltage	Typ. 80 mA
Max. address volume, outputs	32 Byte
Max. address volume, inputs	32 Byte
LED display, product-specific	Error PL: Load supply
Material housing	PA-reinforced PC