

Connecting cable
VMPAL-KM-V-SD44-IP67-
Part number: 562390

FESTO



Data sheet

Feature	Value
Electrical connection	Cable with plug
Cable characteristic	Standard
Min. cable bending radius	115 mm
Cable diameter	9.6 mm
Cable structure	36 x 0.25 mm ²
Degree of protection	IP67 To IEC 60529
Ambient temperature with moving cable	-5 °C...80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	PVC