


Axial kit
EAMM-A-P8-38A-55A
Part number: 562653



Data sheet

Feature	Value
Nominal length	11 mm
Mounting position	optional
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	5.87 kgmm ²
Transmittable torque	12.5 Nm
Product weight	130 g
Interface code, actuator	P8-38A
Interface code, motor in	55A
Interface code, clutch housing	38A
Note on materials	RoHS-compliant