

Solenoid coil VACC-S18-35-A1-1A

Part number: 562907

FESTO



Data sheet

Feature	Value
Type of actuation	Electric
Mounting position	optional
Switching position indicator	no
Duty cycle	100%
Insulation material class	H
Characteristic coil data	24 V AC: 50/60 Hz, power 3.5 VA
Permissible voltage fluctuations	-15%/+10%
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Ambient temperature	-20 °C...60 °C
Product weight	530 g
Electrical connection	Type A Plugs To EN 175301-803
Note on materials	RoHS-compliant
Material solenoid coil	PA Steel