

Adapter
NPFV-AF-G14-G14-MF
Part number: 563398

FESTO



Data sheet

Feature	Value
Nominal size	6 mm
Operating pressure	0.2 MPa...0.8 MPa 2 bar...8 bar
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Note on materials	RoHS-compliant
Material adapter	High-alloy stainless steel
Material seals	NBR