

Branching module MS9-FRM-NG-VS-Y

Part number: 564150

FESTO



Data sheet

Feature	Value
Size	9
Series	MS
Mounting position	optional
Design	Branching module
Operating pressure	0 bar...12 bar
Operational voltage range AC	0 V...250 V
Operational voltage range DC	0 V...125 V
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-10 °C...60 °C
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	1100 g
Type of mounting	Front panel mounting In-line installation With accessories Either:
Pneumatic connection, port 3	1 NPT
Pneumatic connection, port 4	1 NPT
Material covering	PA-reinforced
Note on materials	RoHS-compliant
Material sub-base	Die-cast aluminium
Material mounting bracket	Die-cast aluminium
Material housing	Die-cast aluminium
Material module connector	Die-cast aluminium