

Blanking plug QBC-3/8H-U

Part number: 564788

FESTO



Data sheet

Feature	Value
Size	Standard
Mounting position	optional
Design	Blanking plug Push-pull principle
Size of pack	10
Operating pressure complete temperature range	0.095 MPa...1 MPa 0.95 bar...10 bar 13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C...60 °C 32 °F...140 °F
Product weight	0.071 oz
Pneumatic connection, port 1	Push-in sleeve diameter 3/8"
Note on materials	RoHS-compliant