

Manifold block CPX-P-AB-4XM12-4POL

Part number: 565706

FESTO



Data sheet

Feature	Value
Dimensions (W x L x H)	(incl. interlinking block and connection technology) 50 x 107 x 70 mm
Type of mounting	On interlinking block CPX-M-GE..
Product weight	120 g
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	95 % Non-condensing
Degree of protection	IP65
Corrosion resistance class CRC	2 - Moderate corrosion stress (when installed)
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Electrical connection	4-pin 4x socket A-coded M12x1 round plug connector