

Electrical sub-base VAVE-L1-1VH2-LP

Part number: 566714

FESTO



Data sheet

Feature	Value
Reverse polarity protection	Bipolar
Additional functions	Spark arresting
Signal status display	LED
Nominal operating voltage DC	12 V 24 V
Immunity to surge	0.8 kV
Pollution degree	3
Extended ambient temperature	-5 ... 60° C
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP40
Ambient temperature	-5 °C...50 °C
Mounting position	optional
Product weight	1.5 g
Electrical connection	2-pin Socket
Protective conductor connection	Not available
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS-compliant
Material housing	PA