

Plastic tubing PLN-.-U

Part number: 567449

FESTO



Data sheet

Feature	Value
Operating pressure complete temperature range	-0.095 MPa...0.7 MPa -0.95 bar...7 bar -13.775 psi...101.5 psi
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Note on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Operating medium	Compressed air to ISO 8573-1:2010 [7:::] Water (liquid, ice-free)
LABS (PWIS) conformity	VDMA24364-B2-L
Suitable for use with food	See supplementary material information
Ambient temperature	-22 °F...178 °F
Colour	Blue Brown Yellow Green Natural Red Black Silver White
Note on materials	RoHS-compliant
Material tubing	PE