

Plastic tubing

PEN-3/16-BL-150-CB

Part number: 569890

FESTO

standard O.D tubing, for QS plug connectors, polyethylene (not approved for use in the food industry).

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

| Feature | Value |
|--|--|
| Outer diameter, inches | 3/16 |
| Bending radius relevant for flow rate | 0.075 Fuß |
| Min. bending radius | 0.039 Fuß |
| Temperature dependent operating pressure | -14.4 ... 145 Psi |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:-:-] |
| Ambient temperature | -22 ... 140 °F |
| Product weight according to length | 0.1 oz/ft |
| Colour | blue |
| Shore hardness | D 52 +/-3 |
| Materials note | Conforms to RoHS Free of copper and PTFE |
| Materials information for tubing | PE |