

Adapter
VAVE-C8-1R8
Part number: 571686



Data sheet

Feature	Value
Signal status display	LED
Nominal operating voltage DC	24 V
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 To IEC 60529
Ambient temperature	-5 °C...60 °C
Mounting position	optional
Tightening torque	0.25 Nm
Product weight	3.5 g
Electrical connection	3-pin/2-pin M8/- Plug connector/socket
Protective conductor connection	Not available
Type of mounting	On solenoid valve via M2 central screw
Note on materials	RoHS-compliant
Material housing	PA
Material electrical contact	Bronze