

Blanking plug QBMC-1/8H-U

Part number: 572281

FESTO



Data sheet

Feature	Value
Size	Mini
Mounting position	optional
Design	Blanking plug
Size of pack	10
Operating pressure complete temperature range	0.095 MPa...1 MPa 0.95 bar...10 bar 13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C...60 °C 32 °F...140 °F
Product weight	0.035 oz
Pneumatic connection, port 1	Push-in sleeve Ø 1/8"
Colour of release ring	grey
Note on materials	RoHS-compliant