

# Cover plate VABB-L1-18

Part number: 574482



## Data sheet

| Feature                                   | Value                                      |
|-------------------------------------------|--------------------------------------------|
| Grid dimension                            | 19 mm                                      |
| Operating pressure                        | -0.09 MPa...1 MPa<br>-0.9 bar...10 bar     |
| Approval                                  | RCM trademark<br>c UL us - Recognized (OL) |
| Corrosion resistance class CRC            | 2 - Moderate corrosion stress              |
| LABS (PWIS) conformity                    | VDMA24364-B1/B2-L                          |
| Max. tightening torque for valve mounting | 1.18 Nm                                    |
| Product weight                            | 50 g                                       |
| Note on materials                         | RoHS-compliant                             |
| Material cover plate                      | Wrought aluminium alloy                    |