

Manifold block
VABM-B10-20E-G38-7-P3
Part number: 576446

FESTO



Data sheet

Feature	Value
Grid dimension	22 mm
Mounting position	optional
Max. number of valve positions	7
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	1075 g
Type of mounting	With through-hole
Pilot air port 12	G1/8
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 3	G3/8
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy