

Sealing cap CV-PK-6-B

Part number: 6215

FESTO



Data sheet

Feature	Value
Size of pack	10
Temperature-dependent operating pressure	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...80 °C
Pneumatic connection, port 1	For tubing outer diameter of 8 mm For barbed fitting I.D. 6 mm with union nut
Note on materials	RoHS-compliant
Material cap	TPE-U(PU)