


Selector switch HW-6-38

Part number: 7199



Data sheet

Feature	Value
Valve function	8/6 double solenoid
Standard nominal flow rate (standardised to DIN 1343)	180 l/min
pneumatic working port	M5
Operating pressure	0 bar...8 bar
Type of piloting	Direct
Total leakage	1 l/h
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Nominal torque	1.7 Nm
Tolerance for nominal tightening torque	± 10%
Pneumatic connection, port 1	M5
Pneumatic connection, port 2	M5