

NOT module
VLO-R-M5
Part number: 7422



Data sheet

Feature	Value
Pneumatic connection, port 1	M5
Standard nominal flow rate (standardised to DIN 1343)	80 l/min
Operating pressure	0.001 bar...6 bar
LABS (PWIS) conformity	VDMA24364-B2-L