

Solenoid coil VACS-C-C1-7

Part number: 8025336

FESTO



Data sheet

Feature	Value
Mounting position	optional
Conforms to standard	IEC 61010-1
Duty cycle	100%
Insulation material class	H
Characteristic coil data	48 V DC: 2.4 W
Permissible voltage fluctuations	+/- 10 %
Approval	c UL us - Recognized (OL)
Certificate issuing authority	UL MH18122
Restrictions for environmental and media temperature	-10 - 50°C
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...50 °C
Degree of protection	IP65
Ambient temperature	-10 °C...60 °C
Product weight	37.1 g
Electrical connection	Type C To EN 175301-803
Type of mounting	Via knurled nut
Note on materials	RoHS-compliant
Material housing	PA Steel
Material solenoid coil	Copper Steel Thermoplastic
Material winding	Copper