


Manifold block VABM-B10-30E-G34-5

Part number: 8026362

FESTO



Data sheet

Feature	Value
Grid dimension	32 mm
Mounting position	optional
Max. number of valve positions	5
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	3194 g
Type of mounting	With through-hole
Pilot air port 12	G1/8
Pilot air port 14	G1/8
Pneumatic connection, port 1	G3/4
Pneumatic connection, port 3	G3/4
Pneumatic connection, port 5	G3/4
Note on materials	RoHS-compliant
Material manifold rail	Wrought aluminium alloy