


Separator plate VABD-S1-1-P6-C

Part number: 8029441

FESTO



Data sheet

Feature	Value
Based on standard	ISO 5599-1
Operating pressure	-0.09 MPa...1 MPa -0.9 bar...10 bar
Suitability for vacuum	yes
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C...60 °C
Media temperature	-10 °C...50 °C
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C...50 °C
Product weight	75 g
Note on materials	RoHS-compliant
Material separator plate	Steel NBR