

**Elbow fitting**  
**NPFC-L-2M5-F**  
Part number: 8030208

**FESTO**



**Data sheet**

| Feature                        | Value                                    |
|--------------------------------|------------------------------------------|
| Material threaded fitting      | Nickel-plated brass                      |
| Size of pack                   | 10                                       |
| Operating pressure             | -0.95 bar...50 bar                       |
| Operating medium               | Compressed air to ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress                 |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                        |
| Ambient temperature            | -20 °C...150 °C                          |
| Product weight                 | 8.8 g                                    |
| Pneumatic connection, port 1   | M5                                       |
| Pneumatic connection, port 2   | M5                                       |
| Note on materials              | RoHS-compliant                           |