

**Y-fitting**  
**NPFC-Y-R14-2G14-MFF**  
Part number: 8030232



**Data sheet**

| Feature                        | Value                                     |
|--------------------------------|-------------------------------------------|
| Material threaded fitting      | Nickel-plated brass                       |
| Size of pack                   | 10                                        |
| Operating pressure             | -0.95 bar...50 bar                        |
| Operating medium               | Compressed air to ISO 8573-1:2010 [:-::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress                  |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                         |
| Ambient temperature            | -20 °C...150 °C                           |
| Product weight                 | 40.8 g                                    |
| Pneumatic connection, port 1   | R1/4                                      |
| Pneumatic connection, port 2   | G1/4                                      |
| Note on materials              | RoHS-compliant                            |