

Double nipple NPFC-D-G38-G12-M

Part number: 8030276

FESTO



Data sheet

Feature	Value
Material threaded fitting	Nickel-plated brass
Size of pack	10
Operating pressure	-0.95 bar...50 bar
Operating medium	Compressed air to ISO 8573-1:2010 [:-::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...150 °C
Product weight	35.2 g
Pneumatic connection, port 1	G3/8
Pneumatic connection, port 2	G1/2
Note on materials	RoHS-compliant