

**Extension**  
**NPFC-E2-2G18-FM**  
Part number: 8030302

**FESTO**



**Data sheet**

| Feature                        | Value                                    |
|--------------------------------|------------------------------------------|
| Material threaded fitting      | Nickel-plated brass                      |
| Size of pack                   | 10                                       |
| Operating pressure             | -0.95 bar...50 bar                       |
| Operating medium               | Compressed air to ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress                 |
| LABS (PWIS) conformity         | VDMA24364-B1/B2-L                        |
| Ambient temperature            | -20 °C...150 °C                          |
| Product weight                 | 21.4 g                                   |
| Pneumatic connection, port 1   | G1/8                                     |
| Pneumatic connection, port 2   | G1/8                                     |
| Note on materials              | RoHS-compliant                           |