

Plastic tubing PAN-R-22X2-SW

Part number: 8036207

FESTO



Data sheet

Feature	Value
Outside diameter	22 mm
Flow-relevant bending radius	350 mm
Inside diameter	18 mm
Operating pressure complete temperature range	-0.095 MPa...0.8 MPa -0.95 bar...8 bar -13.775 psi...116 psi
Temperature-dependent operating pressure	-0.095 MPa...1.4 MPa -0.95 bar...14 bar -13.775 psi...203 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-30 °C...80 °C
Product weight according to length	0.131 kg/m
Pneumatic connection	For push-in connector O.D. 22 mm
Colour	Black
Shore hardness	D 62 +/-3
Note on materials	RoHS-compliant
Material tubing	TPE-A