

Input module

CTMM-S1-A-8E-A-M8-4

Part number: 8047506

FESTO



Data sheet

Feature	Value
Dimensions (W x L x H)	27 x 123 x 40 mm
Grid dimension	28 mm
Product weight	75 g
Media temperature	-5 °C...50 °C
Ambient temperature	-5 °C...50 °C
Storage temperature	-20 °C...40 °C
Degree of protection	IP65 IP67
Corrosion resistance class CRC	2 - Moderate corrosion stress
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Max. cable length	30 m
LABS (PWIS) conformity	VDMA24364-B1/B2-L
CE mark (see declaration of conformity)	To EU EMC Directive
Note on materials	RoHS-compliant
Material housing	PA-reinforced
Diagnostics via LED	Errors per module
Number of outputs	0
Nominal operating voltage DC	24 V
Nominal DC operating voltage, electronics/sensors	24 V
Permissible voltage fluctuations for electronics/sensors	± 25%
Intrinsic current consumption at nominal operating voltage for electronics/sensors	Typically 12 mA
Electrical connection input, function	Analogue input
Electrical connection input, connection type	8x socket
Electrical connection input, connector system	M8x1, A-coded to EN 61076-2-104
Electrical connection input, number of connections/cores	4
Number of inputs	8
Max. residual current of inputs per module	0.2 A
Measured variable	Current
analog input	4 - 20 mA

Feature	Value
Isolation channel - channel	no
Isolation channel - internal bus	no
Fuse protection (short circuit)	Internal electronic fuse