

Parallel kit
EAMM-U-60-D32-60RB-91
Part number: 8058932

FESTO



Data sheet

Feature	Value
Size	60
Mounting position	optional
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	26.7 kgmm ²
Frictional torque independent of load	0.07 Nm
Transmittable torque	3 Nm
Product weight	1150 g
Interface code, actuator	D32
Interface code, motor in	60RB
Note on materials	RoHS-compliant