


**Parallel kit**  
**EAMM-U-86-D60-60PA-102**  
Part number: 8058983



**Data sheet**

| Feature                               | Value                 |
|---------------------------------------|-----------------------|
| Size                                  | 86                    |
| Mounting position                     | optional              |
| Max. rotational speed                 | 5000 rpm              |
| LABS (PWIS) conformity                | VDMA24364-B2-L        |
| Storage temperature                   | -25 °C...60 °C        |
| Relative air humidity                 | 0 - 95%               |
| Degree of protection                  | IP40                  |
| Ambient temperature                   | -10 °C...60 °C        |
| Mass moment of inertia                | 175 kgmm <sup>2</sup> |
| Frictional torque independent of load | 0.25 Nm               |
| Transmittable torque                  | 9.5 Nm                |
| Product weight                        | 2500 g                |
| Interface code, actuator              | D60                   |
| Interface code, motor in              | 60PA                  |
| Note on materials                     | RoHS-compliant        |